



Item no: 0213772

GRZ 20-16 LCT-P8 Sprue/Part Plier with long knurled jaw and PNP sensor with plug

- The Standard-Type jaws come with a knurled pattern on the jaw-face to better grip the sprue / part.
- Single action spring return function.
- Fully compatible with SAS's modular EOAT/gripper system.
- Anodized Finish.
- Requirement – Maximum air pressure 87 psi (6 bar).
- Requirement – filtered dry air.

Diameter	0.79 in
Height	0.51 in
Height	0.98 in
Length	1.26 in
Length	4.13 in
Length	1.46 in
Thread	G 1/8 in
Width	0.98 in
Width	1.26 in


---

Force	42 N
-------	------

---

General	
Weight	6 oz

---

Dimensional drawings 

This activity requires login  
Please [login](#) or [register](#) to receive the full benefits of piab.com.

