



Item no: 0213772

GRZ 20-16 LCT-P8 Sprue/Part Plier with long knurled jaw and PNP sensor with plug

- The Standard-Type jaws come with a knurled pattern on the jaw-face to better grip the sprue / part.
- Single action spring return function.
- Fully compatible with SAS's modular EOAT/gripper system.
- Anodized Finish.
- Requirement – Maximum air pressure 87 psi (6 bar).
- Requirement – filtered dry air.

Diameter	20 mm
Height	13 mm
Height	25 mm
Length	32 mm
Length	105 mm
Length	37 mm
Thread	G 1/8 in
Width	25 mm
Width	32 mm

Force	42 N
Sensor type	SP1,5/SN1,5

General	
Weight	170 g

Dimensional drawings 

This activity requires login
Please [login](#) or [register](#) to receive the full benefits of piab.com.

