



Artikelnummer: 0213772

GRZ 20-16 LCT-P8 Sprue/Part Plier with long knurled jaw and PNP sensor with plug

- The Standard-Type jaws come with a knurled pattern on the jaw-face to better grip the sprue / part.
- Single action spring return function.
- Fully compatible with SAS's modular EOAT/gripper system.
- Anodized Finish.
- Requirement – Maximum air pressure 87 psi (6 bar).
- Requirement – filtered dry air.

Diameter	20 mm
Höjd	13 mm
Höjd	25 mm
Längd	32 mm
Längd	105 mm
Längd	37 mm
Gänga	G 1/8 in
Bredd	25 mm
Bredd	32 mm

Force	42 N
-------	------

Generell

Vikt	170 g
------	-------

Måttskiss

Denna aktivitet kräver inloggning
[logga in](#) eller [registrera](#) för att få full nytta av piab.com

