

Suction cup F15MF Thermoelastic polyurethane, M5 male

Item number: F15MF.40.01AC



- **Mark-Free Material.** Made from special thermoelastic polyurethane (TPU), these cups leave no marks or traces on handled objects, ensuring perfect surface integrity for glass, metal, and other sensitive materials.
- **Ideal for Flat Surfaces.** Engineered specifically for flat objects, the F-MF cups provide excellent stability and minimal inherent movement during handling.
- **The design delivers a strong, stable grip** with minimal deformation, making them reliable for precise positioning and parallel lifting.
- **Available in multiple sizes** from 15 to 50 mm, the series covers a broad range of application needs, from small to large flat objects.
- **The material withstands a wide temperature range** and resists common chemicals, making the cups suitable for demanding industrial environments
- **Recommended when the lifting force is parallel** to the surface of the object.

Technical data

Description	Unit	Value
Suction cup shape	-	Flat
Suction cup design	-	Round
Characteristics	-	Mark free
Material	-	TPE
Weight, min.	oz	0.028
Suction cup model	-	F-MF
Volume	in³	0.023
Height	in	0.77
Outer diameter, min.	in	0.65
Fitting size	-	M5
Fitting option	-	None
Fitting style	-	Male
Fitting type	-	M-thread
Fitting material	-	Brass
Suction cup model	-	F15MF
Movement, vertical max.	in	0.039
Curve radius, min.	in	0.67


Performance - Lifting forces

F15MF	Vertical (lb)	Parallel (lb)
5.91 -inHg	0.9	1.012
17.72 -inHg	1.8	2.023
26.58 -inHg	2.7	3.26

Material	
Name	TPE-U
Color	Black
Temperature, min. °F	-4
Temperature max. °F	176
Hardness °Shore A	81

Material resistance	
Alcohol	Good
Concentrated acids	Poor
Ethanol	Not applicable
Hydrolysis	Poor
Methanol	Not applicable
Oil	Excellent
Oxidation	Good
Gasoline	Poor
Wear resistance	Excellent
Weather and ozone	Excellent

Dimensional drawings



Values specified in this data sheet are tested at (unless otherwise stated):

- Room temperature (20°C [68°F] ± 3°C [5.5°F]).
- Standard atmosphere (101.3 [29.9 inHg] ± 1.0 kPa [0.3 inHg]).
- Relative humidity 20-70%.
- Compressed air quality, DIN ISO 8573-1 class 4.

Spare parts

- 01AC | Fitting M5 male, 10–15
- F15MF.40 | Suction cup F15MF Thermoelastic polyurethane