

Suction cup BX20P Polyurethane 60

Item number: BX20P.4E



- Suitable for level adjustment and for uneven and porous surfaces such as cardboard, etc.
- In the two-colored suction cup the bellows and the sealing lip are of different hardnesses, which makes the suction cup strong and stable and, at the same time, soft and flexible.
- DURAFLEX® suction cups manufactured in a specially developed material that features the elasticity of rubber and wear resistance of polyurethane.
- The material DURAFLEX® is mark free.

Technical data

Description	Unit	Value
Suction cup shape	-	Multibellows
Suction cup design	-	Round
Characteristics	-	Mark free
Material	-	Polyurethane (PU)
Weight, min.	oz	0.05
Suction cup model	-	BX-P
Volume	in ³	0.071
Height	in	0.6
Outer diameter, min.	in	0.83
Fitting size	-	None
Fitting option	-	None
Fitting style	-	None
Fitting type	-	None
Fitting material	-	None
Suction cup model	-	BX20P PU60
Movement, vertical max.	in	0.3
Curve radius, min.	in	0.33


Performance - Lifting forces

BX20P PU60	Vertical (lb)	Parallel (lb)
5.91 -inHg	1.079	0.43
17.72 -inHg	1.57	1.16
26.58 -inHg	2.47	1.38

Material	
Name	Polyurethane (PU60)
Color	Green transparent
Temperature, min. °F	50
Temperature max. °F	122
Hardness °Shore A	60

Material resistance	
Alcohol	Not applicable
Concentrated acids	Fair
Ethanol	Fair
Hydrolysis	Fair
Methanol	Poor
Oil	Excellent
Oxidation	Poor
Gasoline	Fair
Wear resistance	Excellent
Weather and ozone	Excellent

Dimensional drawings



Values specified in this data sheet are tested at (unless otherwise stated):

- Room temperature (20°C [68°F] ± 3°C [5.5°F]).
- Standard atmosphere (101.3 [29.9 inHg] ± 1.0 kPa [0.3 inHg]).
- Relative humidity 20-70%.
- Compressed air quality, DIN ISO 8573-1 class 4.

Accessories

- 02AE | Fitting 5xM5 female
- 02AF | Fitting G1/8" male/M5 female, with mesh filter
- 02AA | Fitting M5 female
- 02AB | Fitting G1/8" male, with mesh filter
- 02AC | Fitting 1/8" NPT male, with mesh filter
- 02DD | Fitting G1/8" male/M5 female, with dual flow control valve